

	1	
DESCRIPTION	MATERIAL	QTY.
ESP-SF HINGED FRAME	6063-T6	1
ESP-FF2 RETAINER	6063-T6	1
ESP-FF2 HINGED RETAINER	6063-T6	1
5 15/16" X 3" X 3" X 3/16" ANGLE	6063-T6	4
1 3/4" X 3" X 3" X 3/16" GUSSET	6063-T6	4
	ESP-SF HINGED FRAME ESP-FF2 RETAINER ESP-FF2 HINGED RETAINER 5 15/16" X 3" X 3" X 3/16" ANGLE	ESP-SF HINGED FRAME 6063-T6 ESP-FF2 RETAINER 6063-T6 ESP-FF2 HINGED RETAINER 6063-T6 5 15/16" X 3" X 3/16" ANGLE 6063-T6


D

С

В

 ESP-DF HINGED KIT CONSISTS OF QTY (3) ESP-SF FRAME PIECES, QTY (1) ESP-DF HINGED FRAME PIECE, QTY (4) CORNER ANGLES, QTY (3) ESP-FF2 RETAINERS, QTY (1) ESP-FF2 HINGED RETAINERS, AND QTY (4) RETAINER

2) ANGLES ARE USED TO GUIDE FRAME PIECES INTO POSITION
3) GUSSETS ARE USED TO GUIDE RETAINER PIECES INTO POSITION (IF APPLICABLE)
4) HINGED FRAME SECTION AND HINGED RETAINERS SHOWN TO BE ON TOP OF SIGN CABINET (IF APPLICABLE)
5) SELF DRILLING SCREWS / RIVETS / LOCK CYLINDERS ETC (BY OTHERS) TO SECURE RETAINERS AS NEEDED
6) ANGLES AND GUSSETS TYPICALLY WELDED TO FRAMING (BY OTHERS)
7) 6" - 8" CENTER TO CENTER SPACING RECOMMENDED FOR FLEX CLIPS
8) PIANO HINGES USED TO ALLOW IDS RETAINERS TO HINGE OPEN (IF APPLICABLE)
9) H1 / H1.5 RETAINERS ALLOW SECONDARY FACE TO BE MOUNTED BEHIND PRIMARY FACE
10) EXCELLART UL FILE NUMBER: E152309



4