





2		1	
PART NUMBER	DESCRIPTION	MATERIAL	QTY.
ESP1280466	ESP-SF HINGED FRAME	6063-T6	1
80425, ESP1280420	ESP-FLEX STANDARD AND HINGED FRAME	6063-T6	1
ESP1280415	ESP-BLEED TRIM	6063-T6]
ESP1280139	5 15/16" X 3" X 3" X 3/16" ANGLE	6063-T6	4
ESP1280307	1 3/4" X 3" X 3" X 3/16" GUSSET	6063-T6	4

D

С

В

1) ESP-SF HINGED KIT WITH FLEX STANDARD AND STANDARD TRIM COVER CONSISTS OF QTY (4) ESP-SF HINGED FRAME PIECES, QTY (4) CORNER ANGLES, QTY (3) ESP-FLEX STANDARD FRAME PIECES, QTY (1) ESP-FLEX STANDARD HINGED FRAME PIECE, QTY (4) FRAME GUSSETS, AND QTY (4) BLEED TRIM PIECES 2) ANGLES ARE USED TO GUIDE FRAME PIECES INTO POSITION 3) GUSSETS ARE USED TO GUIDE RETAINER PIECES INTO POSITION
3) GUSSETS ARE USED TO GUIDE RETAINER PIECES INTO POSITION (IF APPLICABLE)
4) HINGED FRAME SECTION AND HINGED RETAINERS SHOWN TO BE ON TOP OF SIGN CABINET (IF APPLICABLE)
5) SELF DRILLING SCREWS / RIVETS / LOCK CYLINDERS ETC (BY OTHERS) TO SECURE RETAINERS AS NEEDED
6) ANGLES AND GUSSETS TYPICALLY WELDED TO FRAMING (BY OTHERS)
7) 6" - 8" CENTER TO CENTER SPACING RECOMMENDED FOR FLEX CLIPS 8) PIANO HINGES USED TO ALLOW IDS RETAINERS TO HINGE OPEN (IF APPLICABLE) 9) H1 / H1.5 RETAINERS ALLOW SECONDARY FACE TO BE MOUNTED BEHIND PRIMARY FACE

EXCELLART SIGN PRODUCTS, LLC.	UNLESS OTHERWISE SPECIFIED:	ASSEMBLY ID:	
1654 S. LONE ELM RD. OLATHE, KS 66061	DIMENSIONS ARE IN INCHES TOLERANCES	ESPH-SF-FLEXBTSF	
(800) 627-9044 SALES@EXCELLART.COM WWW.EXCELLART.COM	FRAC = ±1/32" X.XX = ±0.03 X.XXX = ±0.010 ANGULAR: MACH±1 BEND ±2	DESCRIPTION: ESP-SF HINGED W/ FLEX AND BLEED TRIM	
	REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN	DRAWN BY: APPROVED BY: EXCELLART	
		SIZE Weight: 63.72 (Ibs) REV	
		C Perimeter Length: 19 (ft) -	
A CONTRACTOR OF A CONTRACTOR OFTA CONTRACTOR OFTA CONTRACTOR OFTA CONTRACTOR OFTA CONTRACTOR OFTA CONTRACTOR O	PERMISSION OF EXCELLART SIGN PRODUCTS, LLC IS PROHIBITED.	SCALE: 1:8 1/8/2024 SHEET 3 OF 3	