





2		1	
PART NUMBER	DESCRIPTION	MATERIAL	QTY.
ESP1290201	ESP-4RN FRAME	6063-T6	1
ESP1290202	esp-4n frame	6063-T6]
ESP1280496	ESP-4SI RETAINER	6063-T6]
ESP1281452	2 3/4" X 2" X 2" X 1/8" ANGLE	6063-T6	4

1) ESP-4RN KIT CONSISTS OF QTY (3) ESP-4RN FRAME PIECES, QTY (1) ESP-4N FRAME PIECE, QTY (4) CORNER ANGLES, AND QTY (1) ESP-4SI SNAP-IN RETAINER

D

С

В

2) ANGLES ARE USED TO GUIDE FRAME PIECES INTO POSITION

3) GUSSETS ARE USED TO GUIDE RETAINER PIECES INTO POSITION (IF APPLICABLE)

4) HINGED FRAME SECTION AND HINGED RETAINERS SHOWN TO BE ON TOP OF SIGN CABINET (IF APPLICABLE) 5) SELF DRILLING SCREWS / RIVETS / LOCK CYLINDERS ETC (BY OTHERS) TO SECURE RETAINERS AS NEEDED

6) ANGLES AND GUSSETS TYPICALLY WELDED TO FRAMING (BY OTHERS)

7) 6" - 8" CENTER TO CENTER SPACING RECOMMENDED FOR FLEX CLIPS

8) PIANO HINGES USED TO ALLOW IDS RETAINERS TO HINGE OPEN (IF APPLICABLE)

9) H1 / H1.5 RETAINERS ALLOW SECONDARY FACE TO BE MOUNTED BEHIND PRIMARY FACE

EXCELLART SIGN PRODUCTS, L	LC. UNLESS OTHERWISE SPECIFIED:	ASSEMBLY ID:						
1654 S. LONE ELM RD. OLATHE, KS 66061	DIMENSIONS ARE IN INCHES	ESPS-4RN-4SISF						
(800) 627-9044	$FRAC = \pm 1/32''$ X.XX = ± 0.03	DESCRIPTION:						
SALES@EXCELLART.COM WWW.EXCELLART.COM	X.XXX = ±0.010 ANGULAR: MACH±1 BEND ±2	ESP-4RN KIT						
	REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN	DRAWN BY: EXCELLART			APPROVED BY:		:	
		SIZE	Weigh	nt: 13.0	4	(lbs)	REV	
			C Perimeter Length: 19 (ft) -				-	
A CONTRACTOR OF A CONTRACT OF	PERMISSION OF EXCELLART SIGN PRODUCTS, LLC IS PROHIBITED.		SCALE: 1:8		1/8/2024 SH		SHEET 3 OF 3	
								· .